


Stainless Steel lid with

14mm Rebate



Solid Stainless Steel lid

AT A GLANCE

Capacity: 1 x Clipsal 2000 Series

Style Power/Data/AV Outlet

Lid Material: 304 Grade Stainless

Steel


Lid Size: 180 x 180mm


Box Size: 157 x 157 x 102mm


Recess Size: 177 x 177 x 112mm


This Floor Box Weighs Up To: 2.6KG's

Above View









Conduit Knockouts

Features

Hinged Lid 180 x 180mm, screw fixes to steel box body


2 x Cord Exit Flaps allow cords out with main cover closed

Temporary Cover - Secure to body during concrete pour to prevent ingress of slurry

Steel Box Body - 157 x 157 x 102mm nom. deep. has 10 x combination 25mm/32mm conduit knockouts - 2 on each side and 2 on the base

Outlet Bracket to Suit 1 x Clipsal 2000 Series Style Power/ Data /AV Outlet

Block-out in concrete slab 177 x 177 x 112mm nom. Cut-out in raised floor 159 x 159mm nom. Floating Floor brackets available upon request.



Outlets are not included. All Dimensions quoted are nominal only. Drawings, images and diagrams are for illustrative purposes only and are not to scale. Product details and dimensions are subject to change without notice. This product is not suitable for use in wet areas, is intended for use with fixed wiring only and must be installed by a licensed electrical mechanic in accordance with AS3000, SAA Wiring Rules and A.C.A Requirements



INSTALLATION GUIDE





STEP 1: PREPARE AREA FOR INSTALLATION

OPTION 1. SLAB/ SCREED INSTALLATION

- Secure Steel Box Body housing (157x157x102mm) to structural slab (recommended) or within preformed recess/blockout (177x177x112mm). Ensure Box Body is positioned to finish flush and level with final slab surface and is secured to prevent 'dipping' or 'floating' within screed
- Positioning and securing the Box Body accurately will prevent operation/installation problems at later stages
- Connect conduits to Steel Box Body at desired location(s) and cover opening in box body using the Temporary
 Cover to prevent screed entering the box. Cover screw heads using duct tape, to allow screw removal after screed
 hardens.

IMPORTANT: SEAL ANY GAPS AROUND CONDUIT ENTRIES WITH SEALANT OR DUCT TAPE PRIOR TO SCREEDING IT

OPTION 2. RAISED/ TIMBER FLOOR, DESK OR COUNTER TOP

• Remove & Discard Temporary Cover. Cut aperture (147x147mm) in floor at desired location. The Floor/ Desk/ Counter is then sandwiched between Lid (above) and Steel Box Body (below).

OR

- Remove & Discard Temporary Cover. The Steel Box Body may be dropped into a 159x159mm aperture and screw fixed through the sides near the top opening to prevent it from being lifted out. An adhesive sealant may also provide additional rigidity apply to the area where the Steel Box Body meets the Floor/ Desk/ Counter. Do not attach Floor Box Lid until any adhesive is hardened so as to avoid contact with lid hinges.
- · Optional Floating Floor brackets are available upon request.

STEP 2: FLOOR BOX LID INSTALLATION

- Remove Temporary Cover from Steel Box Body (if not done so already when installing in a raised floor, desk or counter top)
- Lay and trim floor surface (carpet, vinyl, tiles etc) to the size of the FLOOR BOX STEEL BOX BODY for 185 & 185S
- Terminate outlets as required (as per AS3000) fixing them to the mounting bracket supplied and ensuring all metal components maintain earth continuity
- Fit hinged cover using M4 countersunk screws supplied and test the operation of the unit. Floor coverings under the hinge may interfere with operation trim any floor coverings clear of the hinging points.

IMPORTANT: THE LID HINGE POINT SHOULD BE ABOVE THE POWER OUTLET TO ALLOW MAXIMUM ROOM FOR THE CABLES TO EXIT THE FLOORBOX EASILY





